

# WACKER<sup>®</sup> CROSSLINKER V 58

## Curing Agents

WACKER<sup>®</sup> CROSSLINKER V 58 is a Hydrogenpolysiloxane containing reactive Si-H groups.

## Properties

- excellent cure properties of WACKER<sup>®</sup> CROSSLINKER V 58 allow -+ for a low platinum concentration
- low temperature cure
- good release stability
- good anchorage depending on substrates

## Specific features

- Crosslinker
- Solvent-free

## Technical data

### General Characteristics

Property	Condition	Value	Method
Viscosity, dynamic	25 °C	approx. 65 mPa·s	-
Content	-	100 %	-
Appearance	-	clear, colorless, oily liquid	ASTM D 412
Density	25 °C	0.97 g/cm <sup>3</sup>	-

These figures are only intended as a guide and should not be used in preparing specifications.

All the information provided is in accordance with the present state of our knowledge. Nonetheless, we disclaim any warranty or liability whatsoever and reserve the right, at any time, to effect technical alterations. The information provided, as well as the product's fitness for an intended application, should be checked by the buyer in preliminary trials. Contractual terms and conditions always take precedence. This disclaimer of warranty and liability also applies particularly in foreign countries with respect to third parties' rights.

## Applications

- Label
- Release Coatings

## Application details

WACKER® CROSSLINKER V 58 is used in thermal curing of addition-crosslinking solvent-based and solvent-free DEHESIVE® systems.

### Processing:

Batches of coating compound must be prepared in the order given below.

1. First pour in CRA® Modifier in case CRA® is used.
2. Add DEHESIVE® polymer in several portions and stir slowly until the mixture is homogeneous.
3. Thoroughly stir in WACKER® CROSSLINKER V 58 to this mixture.
4. Slowly stir in catalyst.

Local over-concentrations needs to be avoided.

Any contact to alkaline systems needs to be avoided.

## Packaging and storage

### Storage

Store in dry and cool place.

The 'Best use before end' date of each batch is printed on the product label.

Storage in unopened original packaging beyond the date specified on the label does not necessarily mean that the product is no longer usable. In this case however, the properties required for the intended use must be checked for quality assurance reasons.

## Safety notes

Siloxane Crosslinkers should never get into direct contact with concentrated Platinum Catalysts or Alkaline Systems, since this may cause a spontaneous, uncontrolled emission of hydrogen. The formation of hydrogen might lead together with air to the explosive mixtures.

Comprehensive safety information is given in the corresponding Material Safety Data Sheet.

Comprehensive compliance information is given in the the corresponding Product Compliance Sheet.

The sheets are available on request from WACKER subsidiaries or after registration on <http://www.wacker.com>.

## QR Code WACKER® CROSSLINKER V 58



**For technical, quality or product safety questions, please contact:**

**Wacker Chemie AG**, Hanns-Seidel-Platz 4, 81737 Munich, Germany  
[productinformation@wacker.com](mailto:productinformation@wacker.com), [www.wacker.com](http://www.wacker.com)

The data presented in this medium are in accordance with the present state of our knowledge but do not absolve the user from carefully checking all supplies immediately on receipt. We reserve the right to alter product constants within the scope of technical progress or new developments. The recommendations made in this medium should be checked by preliminary trials because of conditions during processing over which we have no control, especially where other companies' raw materials are also being used. The information provided by us does not absolve the user from the obligation of investigating the possibility of infringement of third parties' rights and, if necessary, clarifying the position. Recommendations for use do not constitute a warranty, either express or implied, of the fitness or suitability of the product for a particular purpose.