

# GENIOSIL<sup>®</sup> STP-E15



## Silane-Modified Polymers

Trimethoxysilylpropylcarbamate-terminated polyether

### Properties

GENIOSIL<sup>®</sup> STP-E15 is a polyether-based silane-terminated polymer suitable as a binder in moisture curing formulations. It is a clear liquid with a slight but characteristic odor and differs to conventional silylated polymers due to its high reactivity. This is a direct consequence of the trimethoxysilyl group attached to the organic backbone. It hydrolyzes in the presence of moisture to finally form a stable siloxane network initiated by heavy metal or strong amine catalysis. Formulations are characterized by the following advantages:

- simple compounding with conventional auxiliaries
- plasticizer free if desirable
- good mechanics
- rapid curing
- broad adhesion profile

# Technical data

## General Characteristics

Property	Condition	Value	Method
Viscosity	-	10000 mPas	-
Density	25 °C   1013 hPa	1.0064 g/cm <sup>3</sup>	DIN 51757
Flash point	-	> 250 °C	ISO 2592
Ignition temperature	-	390 °C	DIN 51794

These figures are only intended as a guide and should not be used in preparing specifications.

All the information provided is in accordance with the present state of our knowledge. Nonetheless, we disclaim any warranty or liability whatsoever and reserve the right, at any time, to effect technical alterations. The information provided, as well as the product's fitness for an intended application, should be checked by the buyer in preliminary trials. Contractual terms and conditions always take precedence. This disclaimer of warranty and liability also applies particularly in foreign countries with respect to third parties' rights.

## Applications

- Building & Construction Adhesives
- Do It Yourself
- Flooring Installation
- Home-Improvement Gluing
- Industrial Adhesives
- Silane Modified Polymers

## Application details

GENIOSIL® STP-E15 dissolves readily in standard organic solvents. It is virtually insoluble in aqueous media, and reacts slowly releasing methanol and forming a resinous deposit. Due to its reactive terminal groups GENIOSIL® STP-E15 forms a skin following air exposure after several days. However, its reactivity with water or atmospheric humidity must be taken into account during storage and processing, since the material will slowly start to condense. GENIOSIL® STP-E15 can be formulated by conventional methods and mixing processes. The formulation composition depends on the required property profile. GENIOSIL® STP-E15 can be formulated with a variety of fillers at high addition levels. The range starts with oxides, such as aluminum trihydroxide, quartz powders or pyrogenic silicas, and extends to coated and uncoated chalks. Water scavengers can be added to stabilize the formulations against premature curing as this is moisture-curing technology. Therefore exclusion of moisture during compounding and storage is necessary. GENIOSIL® XL 10 or GENIOSIL® XL 70 are particularly suitable scavengers. Any type of plasticizer can be used to further lower the viscosity as well as to impact elongation values. It has been observed, that polypropylene glycol types give better mechanical performance whereas aromatic plasticizers like trimellitates or phthalates yield good adhesion values. Antioxidants, UV- and light-stabilizers are mandatory to ensure durable sealants and adhesives. The amount and type of stabilizer depends on application needs. Curing of GENIOSIL® STP-E15 requires a catalyst which can be organo-metallic or a strong base compound. Here dioctyl tin or titanium compounds have proven their suitability in the presence of an aminosilane such as GENIOSIL® GF 96. In particular, GENIOSIL® GF 95 can attain improved water resistance, which is further increased by the addition of epoxy silanes. Surface Treatment Always apply the formulation to clean and dry surfaces. GENIOSIL® STP-E15 is used as a reactive binder for adhesives, potting compounds and coatings. Curing takes place at ambient temperature in the presence of both moisture and catalyst. Depending on the formulation, either prepared as one-part or two-part systems, it will give good adhesion to a wide variety of substrates even without pretreatment. The low glass transition temperature allows stable mechanical properties over a wide temperature range.

## Packaging and storage

### Packaging

Information on available container sizes is obtainable from WACKER subsidiaries.

### Storage

The 'Best use before end' date of each batch is shown on the product label. Storage beyond the date specified on the label does not necessarily mean that the product is no longer usable. In this case however, the properties required for the intended use must be checked for quality assurance reasons.

## Safety notes

Comprehensive instructions are given in the corresponding Material Safety Data Sheets. They are available on request from WACKER subsidiaries or may be printed via WACKER web site <http://www.wacker.com>.

## QR Code GENIOSIL® STP-E15



### For technical, quality or product safety questions, please contact:

**Wacker Chemie AG**, Gisela-Stein-Strasse 1, 81671 Munich, Germany  
[productinformation@wacker.com](mailto:productinformation@wacker.com), [www.wacker.com](http://www.wacker.com)

The data presented in this medium are in accordance with the present state of our knowledge but do not absolve the user from carefully checking all supplies immediately on receipt. We reserve the right to alter product constants within the scope of technical progress or new developments. The recommendations made in this medium should be checked by preliminary trials because of conditions during processing over which we have no control, especially where other companies' raw materials are also being used. The information provided by us does not absolve the user from the obligation of investigating the possibility of infringement of third parties' rights and, if necessary, clarifying the position. Recommendations for use do not constitute a warranty, either express or implied, of the fitness or suitability of the product for a particular purpose.